



GS-601 Fusion Splicer

- 6 motors accurate real core to core alignment
- 5 inch high resolution color touch screen
- 6 seconds splicing & 18 seconds heating
- Automatic & real-time ARC calibration
- Industrial quad-core CPU with 30% power saving
- Anti-shock, anti-vibration, dustproof & waterproof
- Apply to 250μm/0.9mm/2.0mm/3.0mm fibers and SOC

Items	Specifications
Alignment method	6 motors core to core alignment
Applicable fiber	SM(G.652), MM(G.651), DS(G.653), NZDS(G.655), BIF(G.657)
Cladding diameter	80-150μm
Coating diameter	160-3000μm
Cleaved length	5-16mm (coating diameter<250μm) 16mm (coating diameter:250-3000μm)
Typical splice loss	SM: 0.02dB; MM: 0.01dB; DS/NZDS/BIF: 0.04dB
Return loss	>60dB
Splicing program	40 groups
Operation mode	Manual/ Automatic
Auto-heating	Available
Typical splice time	6 seconds
Typical heating time	18 seconds for 60mm and 40mm shrinkable sleeves
Fiber magnification	250X(X or Y view), 125X(X and Y view)
Viewing display	Dual high sensitivity camera, 5 inch 800*480 LCD Touch Screen Monitor
Data storage	4000 groups data records
Loss evaluation	Available
Tension test	1.8~2.25N
Interface	GUI menu interface, easy for operation
Battery capacity	5200mAh Li-battery, 250 cycles splicing and heating
Power supply	Adaptor, input: AC100-240V(50/60HZ),output: DC11-13.5V
Electrode life	More than 4000 ARC discharges, easy to replace
Terminals	USB 2.0 port, for software upgrading, records exporting
Operating	Altitude:0-5000m, Humidity:0-95%,Temperature:-10~+50℃; Wind:max 15m/s
Dimension/Weight	156mm(L)×141mm(W)×156mm(H) / 2.45kg (including battery)



Standard Package

Name	Picture	Name	Picture
Fusion Splicer		Power Adapter	
Fiber Cleaver		Power Plug	
Fiber Stripper		User Manual	
Spare Electrodes		Strap	
Cooling tray		Cleaning Brush	
Drop Cable Stripper		Carrying Box	

GS-601 Toolkit Customization



Optional toolkit

1: GS-601 Splicer	3: FHO1000-D28 OTDR	5: FHP12 power meter
2: FHO1000-D22 OTDR	4: MT500 optical power meter	6: VLS-8 VFL
		7: Alcohol pot